

CONFIDENTIAL: THE INFORMATION CONTAINED IN THIS PRESENTATION IS INTENDED TO BE VIEWED BY THE RECIPIENT ONLY AND MUST NOT BE

NEW! AIRTECT ULTIMATE Range of Leak Detection Manifolds

COMPLETE HOT RUNNER PROTECTION DETECT YOUR HOT RUNNER LEAKS EARLY!

Distributed By:

151 Memorial Drive, Unit H Shrewsbury, MA 01545 Tel 888.792.2223 sales@plastixs.com







ULTIMATE RANGE OF DETECTION MANIFOLDS

- New ULTIMATE range of Leak Detection Manifolds incorporate POINT Leak Detection Zones + LOOP Leak Detection Zones in the one Manifold.
- POINT Leak Detection Zones are used for detection of leaking plastic at the Nozzle Gates.
- LOOP Leak Detection Zones are used for detection of leaking plastic at numerous locations on the Hot Runner Manifold.
- LOOP Leak Detection is provided when the Silicone Rubber tubes are Compressed OR Broken due to full circuit design.
- Available in 3 Manifold Sizes. See Later.
- Available as Stand-Alone Manifolds.
- Patent Pending.





LA506-1L-S ULTIMATE LEAK DETECTION MANIFOLD (6-POINT + 1 LOOP FIXED STAND-ALONE TYPE SHOWN)







LA512-2L-S ULTIMATE LEAK DETECTION MANIFOLD (12-POINT+ 2 LOOP STAND-ALONE MODULAR S-TYPE SHOWN)







LA520-2L-S ULTIMATE LEAK DETECTION MANIFOLD (20-POINT+ 2 LOOP STAND-ALONE MODULAR S-TYPE SHOWN)








INSTALLATION EXAMPLE USING LA512-2L-S ULTIMATE STAND ALONE MANIFOLD

POINT Leak Detection Zones:

8 used on the Nozzle Gates (4 unused)

LOOP Leak Detection Zones:

- 1 loop circuit on the Nozzle/Manifold interfaces.
- 1 loop circuit on the Inlet Bushing/Manifold interface.








INSTALLATION EXAMPLE USING LA512-2L-S ULTIMATE STAND ALONE MANIFOLD

POINT Leak Detection Zones:

8 used on the Nozzle Gates (4 unused)

LOOP Leak Detection Zones:

- 1 loop circuit on the Nozzle/Manifold interfaces.
- 1 loop circuit on the Inlet Bushing/Manifold interface.








INSTALLATION EXAMPLE USING LA512-2L-S ULTIMATE STAND ALONE MANIFOLD

POINT Leak Detection Zones:

8 used on the Nozzle Gates (4 unused)

LOOP Leak Detection Zones:

- 1 loop circuit on the Nozzle/Manifold interfaces.
- 1 loop circuit on the Inlet Bushing/Manifold interface.







ULTIMATE RANGE OF MANIFOLDS

PART NUMBER	DESCRIPTION
PART NOIVIDER	DESCRIPTION
LA506-1L-S	6-POINT + 1 LOOP FIXED STAND-ALONE LEAK ALARM MANIFOLD
LA506-1L-S-M-H	6-POINT + 1 LOOP MODULAR STAND-ALONE LEAK ALARM MANIFOLD (HANDLE RELEASE - USE LA508-B BASE UNIT)
LA506-1L-S-M-S	6-POINT + 1 LOOP MODULAR STAND-ALONE LEAK ALARM MANIFOLD (SCREW RELEASE - USE LA508-B BASE UNIT)
LA512-2L-S-M-H	12-POINT + 2 LOOP MODULAR STAND-ALONE LEAK ALARM MANIFOLD (HANDLE RELEASE - USE LA516-B BASE UNIT)
LA512-2L-S-M-S	12-POINT + 2 LOOP MODULAR STAND-ALONE LEAK ALARM MANIFOLD (SCREW RELEASE - USE LA516-B BASE UNIT)
LA520-2L-S-M-H	20-POINT + 2 LOOP MODULAR STAND-ALONE LEAK ALARM MANIFOLD (HANDLE RELEASE - USE LA524-B BASE UNIT)
LA520-2L-S-M-S	20-POINT + 2 LOOP MODULAR STAND-ALONE LEAK ALARM MANIFOLD (SCREW RELEASE - USE LA524-B BASE UNIT)



Distributed By:



151 Memorial Drive, Unit H Shrewsbury, MA 01545 508-842-1606 / 888-842-1606

<u>sales@plastixs.com</u> www.plastixs.com